

DeafPLUS Somerset Mobile Advisory Service

- Hearing aid maintenance clinics
- Equipment demonstrations
- Advice and information through our advice surgeries on the following dates and locations through July

Advice sessions are on an appointment only basis. To make an appointment contact Stewart on 07762 848226, email stewart.weston@deafplus.org or follow us on Facebook Deafplus Somerset

6th July 10.30am-12.30pm Wincanton
Carrington Way Car Park BA9 9JY

6th July 13.30pm-3pm Castle Cary Millbrook
Gardens Car Park BA7 7EE

11th July 10.30am-12.30pm Taunton
Wellsprings Community Church TA2 7NL

14th July 10.30am-12pm Wiveliscombe
Croftway Car Park TA4 2JR

14th July 12.30pm-2.30pm Curry Rivel Village
Green TA10 OHF

19th July 10.30-12.30pm Burnham-on-Sea
Stroke Club, Bay Centre, Cassis Close, TA8
1NN

19th July 1pm-2.30pm Highbridge Bank
Street, Car Park, TA9 3DA

20th July 11am-1pm Somerton St Cleers
Luncheon Club, Polham Lane TA11 6SP

25th July 10.30am-12pm Langport
Cocklemoor Car Park, TA10 9RA

25th July 1.30pm-3pm Shepton Mallet Main
Road by entrance Hospital, Old Wells Road,
BA4 4LP

27th July 1pm-2.30pm Taunton Clifford
Ashman Court, Leslie Avenue TA2 6NL

This month's new products



Geemarc Wake 'n' Shake Vintage £46

Features

Extra loud alarm (80dB)

Flashing ring light

Analogue screen

USB charging for smartphones and other
electronics



Williams AV Pocketalker 2.0 Listener System

£240 with Headset

£260 with Loop

Hear what you want to hear by amplifying the sounds and voices most important to you.

The Pocketalker 2.0 personal listener (sometimes called a personal amplifier) is used to amplify what you want to hear and so helps to reduce distracting background sounds. It is extremely good when used to enhance speech in conversation.

Simply plug the included headphones or earbuds into the headphone socket. Position the Pocketalker so that its microphone is facing what you want to hear and adjust the volume or tone control until the sounds you want to hear are clear and enjoy listening to others again. With more than 60 dB of amplification, it is powerful enough for almost any degree of hearing loss. This personal Assistive Listening Device lets you



communicate effectively one-to-one, even in noisy places!

This slim, ergonomically designed amplifier could not be easier to use.

System includes

PKT 2.0 personal amplifier (includes internal microphone)

Dual stereo isolation earphones

Stereo headphones

Plug-in (no cord) microphone

2 x AAA alkaline batteries

3.5mm male to 3.5mm female cable with mounting clips (12 ft)

Lanyard



**We Sarabec
Baby Monitor
Camera for
Smartphones
£45**

This smart camera connects to your smartphone or tablet using the Wi-Fi signals in your home, it uses 2.4Ghz or 5Ghz Wi-Fi and will alert you in real-time.

The App is available on both the Google Play Store and Apple App Stores.

Features

2.4/5GHz Dual-Band Wi-Fi Connection With the newest dual-band technology, INDOOR1S security camera supports both 2.4GHz and 5GHz channels, which make network connection more stable and smoother.

2K Ultra HD & Night Vision & Full Duplex 2-Way Audio, 2K/3MP Ultra HD/25fps (max) resolution, combined with enhanced night vision technology, displays a clear and crisp video day and night. Enables full two-way audio, contacting with him anytime, anywhere in real-time.

AI Powered Human Motion & Sound Detection The notifications will be sent instantly if any human movement or abnormal sound is detected. AI-powered human motion detection sensitivity can be adjusted to reduce false detection caused by snow or rain. 3-Month Free Cloud Storage & Share via Arenti App Free 3-month of Cloud storage and records a 60-180 second video clip. The video will be saved to the cloud for 72 hours if the cloud storage service is enabled. Meanwhile it is compatible with FAT32 Micro SD cards (sold separately) up to 256G. The device can be shared with your family and friends.



Doro Magna 4000

Amplified sound

Doro Magna 4000 is an elegant choice for

those with moderate to severe hearing impairment. Press the boost button to immediately increase the volume of the handset by +60dB and adjust the tone for an unmistakable sound quality that meets your individual needs. The exceptionally loud ringer is complemented by flashing light when someone is calling. Large buttons and shortcut keys make the phone extremely easy to use. It also features a display for Caller ID, a telephone book, and other functions.

Up to +60dB handset volume

Adjustable tone to suit individual hearing needs

Display for showing names and numbers

X Demonstration models SALE



**PRICE £35.00
(Retailing on
Amazon £66)**

